

TPLUS TUNIC WITH SPLIT LEG & with sleeves (PPE - category III)



FIELD OF APPLICATION

The TPLUS tunic is made with 100% food contact approved stainless steel. It is used by butchers in meat industries, Horeca, supermarkets and many other fields such as textile industry... It ensures cut-protection against any risks with hand knives, hand cutting tools or stabbing.

MATERIAL: Stainless steel chainmail. Food contact

FEATURES

Bust:

- Wire diameter: 0,5 mm
- Internal diameter of the rings: 3 mm
- External diameter of the rings: 4 mm



Sleeve(s): EN ISO 13998 (2003) performance level 1

- Wire diameter: 0,4 mm
- Internal diameter of the rings: 3,2 mm
- External diameter of the rings: 4 mm

Self-closing wrist closure system with stainless steel spring.
Straps attached to the tunic with stainless steel plates
Adjustable waist belt and back strap 100 % polyurethane
(Food contact according to 2002/72/EC regulation) and polyacetal buckles

You can add an hygienic cover or a press-studs apron for maximum hygiene and ease of cleaning.

Blank stainless steel plate on the back (possibility of customized printing on demand)



NORMS & REGULATIONS

This tunic complies with the regulation (UE) EPI 2016/425 (2016).

Bust: EN ISO13998 (2003) performance level 2 (suitable for boning operations).

Sleeves: EN ISO13998 (2003) performance level 1.

Notified body in charge of the certification: N° 00556 Prüf und Zertifizierungsstelle Nahrungsmittel und Verpackung - Fachbereich Nahrungsmittel - Lortzingstrasse 2 - D - 55127 Mainz

Notified body involved in manufacturing control: N° 0333 AFNOR certification
11 rue Francis De Pressensé - 93571 - La Plaine Saint-Denis



CLEANING CONDITIONS

Cleaning / Disinfection: PPE can be cleaned using a suitable washing gun, by soaking, by vigorous brushing or in a washing machine. In all cases, the water with added product must be at a maximum temperature of 63 ° C.

Warning : the technical sheet of the product used refers to a maximum water temperature, which may be lower.

Particular attention to dosage and temperature must be observed in the case of using alkaline chlorinated or acidic products.

Use only products authorized by the veterinary services. The use of chlorine in large doses and at high temperature is not recommended.

Disinfection: High temperature disinfection can be done with clean water of a minimum of 82 ° C up to a maximum temperature of 90 ° C, in a machine, by soaking or sprinkling.

Drying and Storage: Forced drying by hot or natural air ventilation but in a dry and ventilated place. Store in a cool, dry place

N° intrastat : 73239390

Bien plus que la sécurité
More than just safety

TPLUS TUNIC WITH SPLIT LEG & with sleeves (PPE - category III)



SIZE AND REFERENCES

Sleeves	Width x height (cm)	Reference	Weight (grams)	Operator's size (cm)	Waist / chest measurement (cm)
Manches 65 cm <i>Sleeves 65 cm</i>	50 x 100	0XTU730.8S4.710DG5	2580 g	148 - 190	80 - 110
	56 x 115	0XTU730.8M7.710DG5	3140 g	158 - 220	90 - 120
	56 x 125	0XTU730.8M9.710DG5	3260 g	165 - 220	
	64 x 125	0XTU730.8L9.710DG5	3500 g	165 - 220	100 - 140
Manches 75 cm <i>Sleeves 75 cm</i>	56 x 115	0XTU730.8M7.710DG7	3410 g	158 - 220	90 - 120
	64 x 125	0XTU730.8L9.710DG7	3790 g	165 - 220	100 - 140

N° intrastat : 73239390

Bien plus que la sécurité
More than just safety