

Centrifuge Tubes

15 ml / 50 ml polypropylene tubes

- Centrifuge tubes with conical bottom, graduation and writing area
- With screw cap
- Optimal mechanical, thermal and chemical stability
- Light Protection Tubes for light-sensitive materials and reactions

Maximum relative centrifugal forces*:

	188 2xx	210 2xx	227 261	227 270	227 28x
Swinging-bucket rotor	4000 x g	2800 x g	3200 x g	3200 x g	3200 x g
Fixed-angle rotor	15000 x g	11500 x g	17000 x g	17000 x g	9000 x g

^{*} The stated maximum RCF values are guidelines only, depending on a variety of factors such as rotor, temperature, density, pH and type of liquid. The suitability of tubes for a specific application using high centrifugation forces has to be tested.

Key Facts

- Polypropylene
- Graduation and writing area
- Bulk or rack packaging available
- Brown Light Protection Tubes



Ordering Information						
Cat. No.	Product Description	Quantity per Bag	Quantity per Case			
188 261	15 ml tubes, sterile, graduation and writing area	50 (Rack)	500			
188 271	15 ml tubes, sterile, graduation and writing area	100	1000			
188 283	15 ml tubes, light protection tubes, sterile, graduation and writing area	50 (Rack)	500			
188 280	15 ml tubes, light protection tubes, sterile, graduation and writing area	100	1000			
210 261	50 ml tubes, with support skirt, sterile, graduation and writing area	25	450			
210 270	50 ml tubes, with support skirt, sterile, graduation and writing area	25 (Rack)	300			
227 261	50 ml tubes, sterile, graduation and writing area	20	500			
227 270	50 ml tubes, sterile, graduation and writing area	25 (Rack)	300			
227 285	50 ml tubes, sterile, graduation, writing area, white screw cap	20	500			
227 283	50 ml tubes, light protection tubes, sterile, graduation and writing area	25 (Rack)	300			
227 280	50 ml tubes, light protection tubes, sterile, graduation and writing area	20	500			